INTEGRATED CIRCUITS

DATA SHEET

74LVC86AQuad 2-input exclusive OR gate

Product specification
Supercedes data of 1997 Aug 11
IC24 Data Handbook





Quad 2-input exclusive OR gate

74LVC86A

FEATURES

- Wide supply range of 1.2V to 3.6V
- Complies with JEDEC standard no. 8-1A
- Inputs accept voltages up to 5.5V
- CMOS low power consumption
- Direct interface with TTL levels
- 5-volt tolerant inputs, for interfacing with 5-volt logic

DESCRIPTION

The 74LVC86A is a high-performance, low-power, low-voltage Si-gate CMOS device that is pin and superior to most advanced CMOS compatible TTL families.

Inputs can be driven from either 3.3 V or 5 V devices. This feature allows the use of these devices as translators in a mixed 3.3 V/5 V environment.

The 74LVC86A provides the 2-input EXCLUSIVE-OR function.

QUICK REFERENCE DATA

GND = 0 V; $T_{amb} = 25^{\circ}C$; $t_r = t_f \le 2.5 \text{ ns}$

SYMBOL	PARAMETER	CONDITIONS	TYPICAL	UNIT
t _{PHL} t _{PLH}	Propagation delay nA, nB to nYn	$C_L = 50 \text{ pF};$ $V_{CC} = 3.3 \text{ V}$	3.0	ns
C _I	Input capacitance		5.0	pF
C _{PD}	Power dissipation capacitance per gate	$V_{CC} = 3.3 \text{ V}, V_I = \text{GND to } V_{CC}^{-1}$	28	pF

NOTE:

1. C_{PD} is used to determine the dynamic power dissipation (P_D in μW)

 $P_D = C_{PD} \times V_{CC}^2 \times f_i + \Sigma (C_L \times V_{CC}^2 \times f_0)$ where: $f_i = \text{input frequency in MHz; } C_L = \text{output load capacity in pF;}$


f_o = output frequency in MHz; V_{CC} = supply voltage in V;

 $\Sigma (C_L \times V_{CC}^2 \times f_0) = \text{sum of the outputs.}$

ORDERING INFORMATION

OTTO INTO INTO OTTO				
PACKAGES	TEMPERATURE RANGE	OUTSIDE NORTH AMERICA	NORTH AMERICA	PKG. DWG. #
14-Pin Plastic DIL	-40°C to +85°C	74LVC86A N	74LVC86A N	SOT27-1
14-Pin Plastic SO	-40°C to +85°C	74LVC86A D	74LVC86A D	SOT108-1
14-Pin Plastic SSOP Type II	-40°C to +85°C	74LVC86A DB	74LVC86A DB	SOT337-1
14-Pin Plastic TSSOP Type I	-40°C to +85°C	74LVC86A PW	74LVC86APW DH	SOT402-1


PIN CONFIGURATION



PIN DESCRIPTION

PIN NUMBER	SYMBOL	FUNCTION			
1, 4, 9, 12	1A – 4A	Data inpute			
2, 5, 10, 13	1B – 4B	Data inputs			
3, 6, 8, 11	1Y – 4Y	Data outputs			
7	GND	Ground (0 V)			
14	V _{CC}	Positive supply voltage			


LOGIC SYMBOL (IEEE/IEC)



Quad 2-input exclusive OR gate

74LVC86A

LOGIC SYMBOL




INPL	OUTPUTS						
nA	nA nB						
L	L	L					
L	Н	Н					
Н	L	Н					
Н	Н	L					

NOTES:

H = HIGH voltage level
L = LOW voltage level

FUNCTION TABLE

LOGIC DIAGRAM (ONE GATE)



RECOMMENDED OPERATING CONDITIONS

SYMBOL	PARAMETER	CONDITIONS	LIM	UNIT	
STWIBUL	PARAMETER	CONDITIONS	MIN	MAX	UNIT
V	DC supply voltage (for max. speed performance)		2.7	3.6	V
V _{CC}	DC supply voltage (for low-voltage applications)		1.2	3.6	V
VI	DC Input voltage range		0	5.5	V
Vo	DC output voltage range		0	V _{CC}	V
T _{amb}	Operating ambient temperature range in free-air		-40	+85	°C
t _r , t _f	Input rise and fall times	$V_{CC} = 1.2 \text{ to } 2.7V$ $V_{CC} = 2.7 \text{ to } 3.6V$	0 0	20 10	ns/V

ABSOLUTE MAXIMUM RATINGS¹

Absolute Maximum Rating System (IEC 134) Voltages are referenced to GND (ground = 0V)

SYMBOL	PARAMETER	CONDITIONS	RATING	UNIT
V _{CC}	DC supply voltage (for max. speed performance)		-0.5 to +6.5	V
I _{IK}	DC input diode current	V _I < 0	-50	mA
V _I	DC input voltage	Note 2	-0.5 to +5.5	V
I _{OK}	DC output diode current	$V_{O} > V_{CC}$ or $V_{O} < 0$	±50	mA
V _O	DC output voltage	Note 2	-0.5 to V _{CC} + 0.5	V
ΙO	DC output source or sink current	$V_O = 0$ to V_{CC}	±50	mA
I _{GND} , I _{CC}	DC V _{CC} or GND current		±100	mA
T _{stg}	Storage temperature range		-65 to +150	°C
P _{TOT}	Power dissipation per package – plastic mini-pack (SO) – plastic shrink mini-pack (SSOP and TSSOP)	above +70°C derate linearly with 8 mW/K above +60°C derate linearly with 5.5 mW/K	500 500	mW

NOTES:

- 1. Stresses beyond those listed may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- 2. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

Quad 2-input exclusive OR gate

74LVC86A

DC CHARACTERISTICS

Over recommended operating conditions voltages are referenced to GND (ground = 0V)

			L	IMITS				
SYMBOL	PARAMETER	TEST CONDITIONS	Temp = -	Temp = -40°C to +85°C				
			MIN	TYP ¹	MAX			
V	HICH level lanut voltage	V _{CC} = 1.2V	V _{CC}					
V _{IH}	HIGH level Input voltage	V _{CC} = 2.7 to 3.6V	2.0			1		
V	LOW/ lovel langut valtage	V _{CC} = 1.2V			GND	V		
V _{IL}	LOW level Input voltage	V _{CC} = 2.7 to 3.6V			0.8]		
		$V_{CC} = 2.7V$; $V_I = V_{IH}$ or V_{IL} ; $I_O = -12mA$	V _{CC} - 0.5					
	HIGH level output voltage	$V_{CC} = 3.0V$; $V_I = V_{IH}$ or V_{IL} ; $I_O = -100\mu A$	V _{CC} -0.2	V _{CC}		٧		
V _{OH}		$V_{CC} = 3.0V$; $V_I = V_{IH}$ or V_{IL} ; $I_O = -18$ mA	V _{CC} -0.6					
		$V_{CC} = 3.0V$; $V_I = V_{IH}$ or V_{IL} ; $I_O = -24$ mA	V _{CC} -0.8	V _{CC} -0.8		1		
		$V_{CC} = 2.7V$; $V_I = V_{IH}$ or V_{IL} ; $I_O = 12$ mA			0.40			
V _{OL}	LOW level output voltage	$V_{CC} = 3.0V$; $V_I = V_{IH}$ or V_{IL} ; $I_O = 100\mu A$			0.20	V		
		$V_{CC} = 3.0V$; $V_I = V_{IH}$ or V_{IL} ; $I_O = 24$ mA			0.55			
ł _l	Input leakage current	V _{CC} = 3.6V; V _I = 5.5V or GND		±0.1	±5	μА		
I _{CC}	Quiescent supply current	$V_{CC} = 3.6V; V_I = V_{CC} \text{ or GND}; I_O = 0$		0.1	10	μΑ		
Δl _{CC}	Additional quiescent supply current per input pin	$V_{CC} = 2.7V$ to 3.6V; $V_I = V_{CC} - 0.6V$; $I_O = 0$		5	500	μА		

NOTES:

AC CHARACTERISTICS

GND = 0 V; t_r = $t_f \leq$ 2.5 ns; C_L = 50 pF; R_L = 500 Ω ; T_{amb} = -40°C to +85°C

			LIMITS							
SYMBOL	PARAMETER	WAVEFORM	$V_{CC} = 3.3V \pm 0.3V$			V _{CC} = 2.7V			V _{CC} = 1.2V	UNIT
		I	MIN	TYP ¹	MAX	MIN	TYP ¹	MAX	TYP	
t _{PHL} / t _{PLH}	Propagation delay nA, nB to nY	Figures 1, 2	1.5	3.0	5	1.5	3.4	5.8	11	ns

NOTE:

AC WAVEFORMS

 V_M = 1.5 V at $V_{CC} \ge 2.7 \text{ V}$

 V_{M}^{N} = 0.5 • V_{CC} at V_{CC} < 2.7 V V_{OL} and V_{OH} are the typical output voltage drop that occur with the output load.




Figure 1. Input (nA, nB) to output (nY) propagation delays

TEST CIRCUIT




Figure 2. Load circuitry for switching times.

^{1.} All typical values are at V_{CC} = 3.3V and T_{amb} = 25°C.


^{1.} These typical values are at V_{CC} = 3.3V and T_{amb} = 25°C.

Quad 2-input exclusive OR gate

74LVC86A

DIP14: plastic dual in-line package; 14 leads (300 mil)

SOT27-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

UNIT	A max.	A ₁ min.	A ₂ max.	b	b ₁	С	D ⁽¹⁾	E ⁽¹⁾	e	e ₁	L	ME	Мн	w	Z ⁽¹⁾ max.
mm	4.2	0.51	3.2	1.73 1.13	0.53 0.38	0.36 0.23	19.50 18.55	6.48 6.20	2.54	7.62	3.60 3.05	8.25 7.80	10.0 8.3	0.254	2.2
inches	0.17	0.020	0.13	0.068 0.044	0.021 0.015	0.014 0.009	0.77 0.73	0.26 0.24	0.10	0.30	0.14 0.12	0.32 0.31	0.39 0.33	0.01	0.087

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.


OUTLINE		REFER	EUROPEAN	ISSUE DATE			
VERSION	IEC	IEC JEDEC EIAJ				ISSUE DATE	
SOT27-1	050G04	MO-001AA				92-11-17 95-03-11	

Quad 2-input exclusive OR gate

74LVC86A

SO14: plastic small outline package; 14 leads; body width 3.9 mm

SOT108-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	1.75	0.25 0.10	1.45 1.25	0.25	0.49 0.36	0.25 0.19	8.75 8.55	4.0 3.8	1.27	6.2 5.8	1.05	1.0 0.4	0.7 0.6	0.25	0.25	0.1	0.7 0.3	8°
inches	0.069	0.010 0.004	0.057 0.049	0.01		0.0100 0.0075		0.16 0.15	0.050	0.244 0.228	0.041	0.039 0.016		0.01	0.01	0.004	0.028 0.012	o°

Note

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	EIAJ		PROJECTION	ISSUE DATE
SOT108-1	076E06S	MS-012AB				95-01-23 97-05-22


1998 Apr 28 6

Quad 2-input exclusive OR gate

74LVC86A

SSOP14: plastic shrink small outline package; 14 leads; body width 5.3 mm

SOT337-1



DIMENSIONS (mm are the original dimensions)

UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	Ø	٧	w	у	Z ⁽¹⁾	θ
mm	2.0	0.21 0.05	1.80 1.65	0.25	0.38 0.25	0.20 0.09	6.4 6.0	5.4 5.2	0.65	7.9 7.6	1.25	1.03 0.63	0.9 0.7	0.2	0.13	0.1	1.4 0.9	8° 0°

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE			
VERSION	IEC	JEDEC	EIAJ		PROJECTION	1330E DATE	
SOT337-1		MO-150AB				95-02-04 96-01-18	


1998 Apr 28 7


Quad 2-input exclusive OR gate


74LVC86A


TSSOP14: plastic thin shrink small outline package; 14 leads; body width 4.4 mm


SOT402-1











DIMENSIONS (mm are the original dimensions)

UNIT	A max.	Α1	A ₂	A ₃	bр	c	D ⁽¹⁾	E ⁽²⁾	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	1.10	0.15 0.05	0.95 0.80	0.25	0.30 0.19	0.2 0.1	5.1 4.9	4.5 4.3	0.65	6.6 6.2	1.0	0.75 0.50	0.4 0.3	0.2	0.13	0.1	0.72 0.38	8° 0°

Notes

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

	OUTLINE		EUROPEAN	ISSUE DATE			
VERSION		IEC	JEDEC	EIAJ	PROJECTION	ISSUE DATE	
	SOT402-1		MO-153			-94-07-12 95-04-04	

1998 Apr 28 8

Quad 2-input exclusive OR gate

74LVC86A

NOTES

Quad 2-input exclusive OR gate

74LVC86A

DEFINITIONS						
Data Sheet Identification	Product Status	Definition				
Objective Specification	Formative or in Design	This data sheet contains the design target or goal specifications for product development. Specifications may change in any manner without notice.				
Preliminary Specification	Preproduction Product	This data sheet contains preliminary data, and supplementary data will be published at a later date. Philips Semiconductors reserves the right to make changes at any time without notice in order to improve design and supply the best possible product.				
Product Specification	Full Production	This data sheet contains Final Specifications. Philips Semiconductors reserves the right to make change at any time without notice, in order to improve design and supply the best possible product.				

Philips Semiconductors and Philips Electronics North America Corporation reserve the right to make changes, without notice, in the products, including circuits, standard cells, and/or software, described or contained herein in order to improve design and/or performance. Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified. Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

LIFE SUPPORT APPLICATIONS

Philips Semiconductors and Philips Electronics North America Corporation Products are not designed for use in life support appliances, devices, or systems where malfunction of a Philips Semiconductors and Philips Electronics North America Corporation Product can reasonably be expected to result in a personal injury. Philips Semiconductors and Philips Electronics North America Corporation customers using or selling Philips Semiconductors and Philips Electronics North America Corporation Products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors and Philips Electronics North America Corporation for any damages resulting from such improper use or sale.

Philips Semiconductors 811 East Arques Avenue P.O. Box 3409 Sunnyvale, California 94088–3409 Telephone 800-234-7381 © Copyright Philips Electronics North America Corporation 1998 All rights reserved. Printed in U.S.A.

print code Date of release: 05-96

Document order number: 9397-750-04488

Let's make things better.

Philips Semiconductors



