

博穆电子有限公司

BOMU ELECTRONICS CO., LTD

PH 条形连接器 (2.00mm)

技术参数 TECHNICAL PARAMETER

间距(PITCH):2.00mm

极数(Poles):2--12

适用基板厚度(Applicable PC board thickness):1.6mm

额定电流(Current rating):5A,AC,DC

额定电压(Voltage rating):250V,AC,DC

工作温度(Working Temperature):-25℃~+85℃

耐压值(Withstand voltage):1500V,AC/min

接触电阻(Contact resistance): $\leq 0.01 \Omega$

绝缘电阻(Insulation resistance): $\geq 1000M \Omega$

极数 Poles	编号 Part Number		尺寸 Dimensions(mm)	
			A	B
2	PH-2A	PH-2AW	2.0	6
3	PH-3A	PH-3AW	4	8
4	PH-4A	PH-4AW	6	10
5	PH-5A	PH-5AW	8	12
6	PH-6A	PH-6AW	10	14
7	PH-7A	PH-7AW	12	16
8	PH-8A	PH-8AW	14	18
9	PH-9A	PH-9AW	16	20
10	PH-10A	PH-10AW	18	22
11	PH-11A	PH-11AW	20	24
12	PH-12A	PH-12AW	22	26

材料 MATERIAL

基座(HOUSING):尼龙66UL94V-0(NYLON66 UL94V-0)
插针(PIN):黄铜(BRASS)表面镀纯锡(PURE TIN-PLATED)

