




Electrical Characteristics:
 Current rating: 0.5A AC/DC
 Voltage rating: 50V AC/DC
 Temperature range: -25°C~+85°C
 Withstand Voltage: 500V AC/Minute
 Contact Resistance: ≤20mΩ
 Insulation resistance: ≥800mΩ
 Relative Humidity: 93%+40°C

Material Description:
 Contact: Phosphor Bronze Tin-Leadplated
 Solder Tab: Phosphor Bronze Tin-plated
 Housing: Thermoplastic(UL94V-0)
 Slider: Thermoplastic(UL94V-0)



| PIN数 | DIM=A | DIM=B | DIM=C | DIM=D |
|------|-------|-------|-------|-------|
| 30P | 36.4 | 29.00 | 37.0 | 31.10 |
| 29P | 35.4 | 28.00 | 36.0 | 30.10 |
| 28P | 34.4 | 27.00 | 35.0 | 29.10 |
| 27P | 33.4 | 26.00 | 34.0 | 28.10 |
| 26P | 32.4 | 25.00 | 33.0 | 27.10 |
| 25P | 31.4 | 24.00 | 32.0 | 26.10 |
| 24P | 30.4 | 23.00 | 31.0 | 25.10 |
| 23P | 29.4 | 22.00 | 30.0 | 24.10 |
| 22P | 28.4 | 21.00 | 29.0 | 23.10 |
| 21P | 27.4 | 20.00 | 28.0 | 22.10 |
| 20P | 26.4 | 19.00 | 27.0 | 21.10 |
| 19P | 25.4 | 18.00 | 26.0 | 20.10 |
| 18P | 24.4 | 17.00 | 25.0 | 19.10 |
| 17P | 23.4 | 16.00 | 24.0 | 18.10 |
| 16P | 22.4 | 15.00 | 23.0 | 17.10 |
| 15P | 21.4 | 14.00 | 22.0 | 16.10 |
| 14P | 20.4 | 13.00 | 21.0 | 15.10 |
| 13P | 19.4 | 12.00 | 20.0 | 14.10 |
| 12P | 18.4 | 11.00 | 19.0 | 13.10 |
| 11P | 17.4 | 10.00 | 18.0 | 12.10 |
| 10P | 16.4 | 9.00 | 17.0 | 11.10 |
| 9P | 15.4 | 8.00 | 16.0 | 10.10 |
| 8P | 14.4 | 7.00 | 15.0 | 9.10 |
| 7P | 13.4 | 6.00 | 14.0 | 8.10 |
| 6P | 12.4 | 5.00 | 13.0 | 7.10 |
| 5P | 11.4 | 4.00 | 12.0 | 6.10 |
| 4P | 10.4 | 3.00 | 11.0 | 5.10 |

| SER | AREA | REVISIONS | CHK | DATE | UNLESS OTHERWISE SPECIFIED TOLERANCES ARE |
|-----|------|-----------|-----|------|---|
| △ | | | | | X.X ±0.15 |
| △ | | | | | X.XX ±0.05 |
| △ | | | | | X.XXX |
| △ | | | | | ANG. ±0°30' |
| △ | | | | | UNIT MM |

深圳市钜硕电子有限公司

| | | | |
|----------|-----------|--------------|---------------|
| APPROVED | DATE | PART NO. | 1. OK-FX-NPWB |
| CHECKED | DATE | DRAWING NO. | JUSHUO |
| DRAWN | DATE | COMPUTER NO. | |
| 杨帆 | 2004.6.16 | SCALE | A3 |
| NUMBER | 81 | SIZE | A |