



Technical data:

Housing :PBT (UL94V-0). Black

Terminal:S. Ø0.64mm Brass, Gold plating

Current Rating :1Amp Max.

Dielectric Withstanding Voltage:

600V AC R. M. S. for one minute.

Insulation Resistance :5000M ohms Min

AT 500V DC

Contact Resistance :30m ohms Max.

Operating Temperature : -55°C to+105°C

Max Processing Temp :220°C for 10 seconds.

3 ≤ R ≤ 40

筒牛2.54-2xnP

未注尺寸公差 为±0.05	绘制	郝世彦	图号	
未注角度公差 为±2°	审核		客户	
	核准		客户料号	
	供应商		单位	mm
	比例		页次	