



Technical data:

Housing :PBT (UL94V-0). Black

Terminal:S. Ø0.64mm Brass, Gold plating

Current Rating :1Amp Max.

Dielectric Withstanding Voltage:

600V AC R. M. S. for one minute.

Insulation Resistance :5000M ohms Min

AT 500V DC

Contact Resistance :30m ohms Max.

Operating Temperature : -55°C to+105°C

Max Processing Temp :220°C for 10 seconds.

3 ≤ R ≤ 40

筒牛2.54-2xnP

|                  |     |     |      |    |
|------------------|-----|-----|------|----|
| 未注尺寸公差<br>为±0.05 | 绘制  | 郝世彦 | 图号   |    |
| 未注角度公差<br>为±2°   | 审核  |     | 客户   |    |
|                  | 核准  |     | 客户料号 |    |
|                  | 供应商 |     | 单位   | mm |
|                  | 比例  |     | 页次   |    |