



PCB LAYOUT

备注：侧弹分为外弹与内弹

NOTES:

- Housing: Thermoplastics, UL94V-0
- Contact: Copper Alloy
- Shell: Copper Alloy/Steel
- Voltage Current Rating: 1.5 AMP. 30V AC
- Insulation Resistance: 1000MΩ Min.
- Contact Resistance: 30 MΩ Max.
- Dielectric Withstanding Voltage: 500W AC
- Temperature Range: -35°C to +85°C
- Insulator color: Black/White
- Plastic material: PBT/LCP/Others
- Shell finish: Nickel plated/Tin-Lead plated
- Mechanical:
- Mating Force: 3.5KG MAX
- Umating Force: 0.7 KG MIN.
- Contact finish:
- 01: Selective Gold Flash
- 02: Selective Gold 3U”
- 03: Selective Gold 5U”
- 04: Selective Gold 15U”
- 05: Selective Gold 30U”

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

| 公差  | UNIT  | 比例    | 日期         | 制图      | 审核   | 产品料号             | 产品名称           | 角法   | 版本  |
|-----|-------|-------|------------|---------|------|------------------|----------------|------|-----|
| 公差  | UNITS | SCALE | DATE       | DRAWING | CHKD | PRODUCT PART NO. | PRODUCT NAME   | VIEW | VER |
| X   | ±0.25 | 1:1   | 2009/10/20 |         |      |                  | USB A母插座无边方脚有柱 |      |     |
| X   | ±0.20 | ±2    |            |         |      |                  |                |      |     |
| XX  | ±0.15 | ±1    |            |         |      |                  |                |      |     |
| XXX | ±0.10 | ±0.5  |            |         |      |                  |                |      |     |