








REV.	ECH NO	LOCATIONS	DESCRIPTION	DATE



- Note:
- 1.Material:
- 1.1 Housing: High temperature thermoplastic with g.f,UL94V-0
- 1.2 Contact: copper alloy,t=0.15mm
- 1.3 Shell: copper alloy,t=0.30mm
- 2.Specification:
- 2.1 Current rating: 1 A Max.
- 2.2 Dielectric withstanding voltage: 100 V(ac) for 1 min.
- 2.3 Contact resistance: 50 mW Max.
- 2.4 Insulation resistance: 100 MW Min.
- 2.5 Total mating force: 3.57 Kgf Max.
- 2.6 Total unmating force: 1.0 Kgf Min.0.81~2.05 Kgf Min.
- 2.7 Temperature range: -30°C~80°C

A 01 S B 1 4 1 B 1-067

- ① 产品代号 A:成品
- ② 产品系列 01:micro usb 5p in
- ③ 产品类别 S:母座
- ④ 产品类型 B:B TYPE
- ⑤ 外壳材质 1:CB300R-H
- ⑥ 端子材质 4:55101r-BH
- ⑦ 主体材质 1:1CP
- ⑧ 主体颜色 B:黑色
- ⑨ 下板类型 1:20P
- ⑩ 细节流水 007:11002 008:5 B TYPE 四脚全插牛角型短针

PART NO:	A01SB141B1-067		MATERIAL:	SEE NOTE	
MODEL NO:	XX		FINSH:	SEE NOTE	
UNIT:	MM	SIZE:	A4	COLOR:	SEE NOTE
TOLERANCE UNSPECIFIED			DR:	夏友红	
.x			CHK:		
.xx			APP:		
.xxx			SCALE:	5:1	DATE: 2012.05.02
Ang			DWG NO:	A067	REV: B
			TITLE: MICRO USB 5S B TYPE 四脚全插牛角型短针		