



目錄 MAPX	變更內容 MODIFICATION	日期 DATE
------------	----------------------	------------



RECOMMENDED PCB PATTERN LAYOUT

- NOTES:
- Housing: Thermoplastics, UL94V-0
  - Contact: Copper Alloy
  - Shell: Copper Alloy/Steel
  - Voltage Current Rating: 1.5 AMP, 30V AC
  - Insulation Resistance: 1000MΩ Min.
  - Contact Resistance: 30 MΩ Max.
  - Dielectric Withstanding Voltage: 500W AC
  - Temperature Range: -35°C to +85°C
  - Insulator color: Black/White
  - Plastic material: PBT/LCP/Others
  - Shell finish: Nickel plated/Tin-Bead plated
  - Mechanical:
    - Mating Force: 3.5KG MAX
    - Umating Force: 0.7 KG MIN.
  - Contact finish:
    - 01: Selective Gold Flash
    - 02: Selective Gold 3U"
    - 03: Selective Gold 5U"
    - 04: Selective Gold 15U"
    - 05: Selective Gold 30U"

备注：侧弹分为外弹与内弹

产品图  
PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE	公差	UNIT	比例	SCALE	日期	DATE	制图	DRAWING	7-V-B	产品料号	PRODUCT PART NO.	产品名称	角法	版本	VER
X	±0.15	X'	±5°	1:1	2011.10.10		审核			USB-AF外扣弯脚				A0	
X	±0.10	X'	±2°				核准								
XX	±0.05	XX'	±1°												
XXX	±0.03	XXX'	±0.5°												