



备注：侧弹分为外弹与内弹

目錄 MAPX	變更內容 MODIFICATION	日期 DATE
------------	----------------------	------------

- NOTES:
- Housing: Thermoplastics, UL94V-0
 - Contact: Copper Alloy
 - Shell: Copper Alloy/Steel
 - Voltage Current Rating: 1.5 AMP. 30V AC
 - Insulation Resistance: 1000MΩ Min.
 - Contact Resistance: 30 MΩ Max.
 - Dielectric Withstanding Voltage: 500W AC
 - Temperature Range: -35°C to +85°C
 - Insulator color: Black/White
 - Plastic material: PBT/LCP/Others
 - Shell finish: Nickel plated/Tin-Lead plated
 - Mechanical:
 - Mating Force: 3.5KG MAX
 - Umating Force: 0.7 KG MIN.
 - Contact finish:
 - 01: Selective Gold Flash
 - 02: Selective Gold 3U”
 - 03: Selective Gold 5U”
 - 04: Selective Gold 15U”
 - 05: Selective Gold 30U”

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNITS	UNLESS OTHERWISE SPECIFIED
X	±0.15
X	±0.10
.XX	±0.05
.XXX	±0.03

单位 UNITS	MM	制图 DRAWING	Z-Y-B	产品料号 PRODUCT PART NO.
比例 SCALE	1:1	审核 CHECK		USB-A17沉板
日期 DATE	2009/10/20	核准 APPR		
			角法 VIEW	版本 VER
				A0