



目錄 MAPX	變更內容 MODIFICATION	日期 DATE
Δ	側彈變更	2013. 3. 10

NOTES:

Housing: Thermoplastics, UL94V-0

Contact: Copper Alloy

Shell: Copper Alloy/Steel

Voltage Current Rating: 1.5 AMP. 30V AC

Insulation Resistance: 1000MΩ Min.

Contact Resistance: 30 MΩ Max.

Dielectric Withstanding Voltage: 500W AC

Temperature Range: -35°C to +85°C

Insulator color: Black/White

Plastic material: PBT/LCP/Others

Shell finish: Nickel plated/Tin-Lead plated

Mechanical:

Mating Force: 3.5KG MAX

Umating Force: 0.7 KG MIN.

Contact finish:

01: Selective Gold Flash

02: Selective Gold 3U”

03: Selective Gold 5U”

04: Selective Gold 15U”

05: Selective Gold 30U”

备注：侧弹分为外弹与内弹

产品图

PRODUCT CHART DWG

公差一览表

公差一览表 TOLERANCE UNLESS OTHERWISE	单位 UNITS	制图 DRAWING	产品料号 PRODUCT PART NO.
X ±0.25	MM	Z-Y-B	产品名称 PRODUCT NAME
X ±0.20	1:1	审核 CHECK	USB A母贴板方脚有柱
XX ±0.15	SCALE	核准 APPD	角法 VIEW
XXX ±0.10	DATE	2009. 10. 20	版本 VERS
			A0

