








PRODUCT NO.	DISC02LSGET
ROHS compliant	



**RECOMMENDED P.C.B. LAYOUT (TOP VIEW)**



- NOTES :
- 1>.Specification:
    - 1>.Operating force:1000gf Max
    - 2>.Operating Temperature: -40° to+85°
    - 3>.Storage Temperature: -40° to+85°
    - 4>.Mechanical Life:3000cycles minimum
    - 5>.Electrical Life:2000cycles minimum
  2. PLATING:
    - GOLD FLASH 1u"(min.) SOLDER TAIL,
    - 3u" GOLD PLATING ON THE CONTACT AREA,
    - WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION

- DISC XX I S G E T
- [包裝方式: I=卷裝 R=盒裝]
  - [電鍍層: B=鍍鍍銀3u" G=鍍鍍銀3u" / 鍍鍍銀1-2u"]
  - [G=鍍金 S=內金外鍍]
  - [觸頭: S鋼 / 1鋼 / 0鋼 / A鋼 / Z鋼]
  - [T=低接觸度 S=低接觸度 L=長推]
  - [產品碼: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]

Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u"Gold

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION	
LINER	ANGLES	COPY	PROJECTION
0 ± 0.25	0. ± 2'		
.00 ± 0.15	.0 ± 1'		
.000± 0.10	.00± 0.5'		
DESIGN	kathy	2012/04/12	
DRAWING			
CHECK			
APPRO.			

**RE** 东莞市广誉实业有限公司  
Dongguan Kingtek Industrial Co., Ltd.

FILE NO.	DISC02LSGET-A
SIZE	UNIT SCALE SHEET REV.
A4	mm 2 : 1 1OF 1 A