








PRODUCT NO.	1
DISC10L.SGSET	RoHS compliant



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

- NOTES :
- 1> Specification:
 - 1> Operating force: 10000gf Max
 - 2> Operating Temperature: -40° to+85°
 - 3> Storage Temperature: -40° to+85°
 - 4> Mechanical Life: 3000cycles minimum
 - 5> Electrical Life: 2000cycles minimum
 2. PLATING:
 - GOLD FLASH 1u"(min.) SOLDER TAIL,
 - 3u" GOLD PLATING ON THE CONTACT AREA,
 - WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION



(Construction)

Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u"Gold

TOLERANCE UNLESS OTHERWISE SPECIFIED			INSPECTION COPY	
LINER	ANGLES	PROJECTION	COPY	
0 ± 0.25	0 ± 2°		BY DISC SERIES PITCH 2.54mm	
.00 ± 0.15	.0 ± 1°		PRODUCT FAMILY DISC SERIES	
.000 ± 0.10	.00 ± 0.5°	DESIGN	PRAT NO.	DISC10L.SGSET
DRAWING			FILE NO.	DISC10L.SGSET-A
CHECK			SIZE	UNIT SCALE SHEET REV.
APPRO.			A4	mm 2 : 1 1 OF 1 A

东莞市广誉实业有限公司
Dongguan Kingtek Industrial Co., Ltd.

REV.	RCN NO.	DR	DATE