


高压电容（直插）

68PF 1KV 10%


标称容量: 68PF

容量允许偏差: $\pm 10\%$

额定电压: 1KV



尺寸大小



D: $5.0 \pm 0.5\text{mm}$ F: $5.0 \pm 0.5\text{mm}$ d: $0.50 \pm 0.06\text{mm}$ L: $20 \pm 0.5\text{mm}$ T: $\leq 4\text{mm}$