


MAPX	MODIFICATION	DATE



NOTES:

1. HOUSING: SEE NOTES,  
TERMINAL: SEE NOTES.  
SHELL: SEE NOTES.

SPECIFICATION:

1. ELECTRICAL CHARACTERISTIC:  
CONTACT RESISTANCE:  $30M\Omega$  MAX  
DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN  
INSULATION RESISTANCE:  $1000M\Omega$  MIN
2. MECHANICAL CHARACTERISTIC:  
INSERTION FORCE: 35N(3.57KGF) MAX  
EXTRACTION FORCE:  $10 \sim 35N(1.02 \sim 3.57KGF)$  MIN  
DURABILITY: 1500 CYCLES EXTRACTION FORCE:  $10 \sim 35N$   
3000 CYCLES MIN  
5000 CYCLES EXTRACTION FORCE:  $3 \sim 35N$
3. ENVIRONMENTAL:  
OPERATING TEMPERATURE:  $-55^{\circ}C + 85^{\circ}C$
4. Contact finish:  
01: Selective Gold Flash  
02: Selective Gold 3U"  
03: Selective Gold 5U"  
04: Selective Gold 15U"  
05: Selective Gold 30U"

<p>产品图 PRODUCT CHART DWG</p> <p>公差一览表 TOLERANCE UNLESS OTHERWISE</p>				单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.			
X.	$\pm 0.25$	X.	$\pm 5^{\circ}$	比例 SCALE	1:1	审核 CHKD		产品名称 PRODUCT NO.	C42513		
.X	$\pm 0.20$	.X	$\pm 2^{\circ}$	日期 DATE	2015.01.10	核准 APPD		角法 VIEW		版本 VER	A0
.XX	$\pm 0.15$	.XX	$\pm 1^{\circ}$								
.XXX	$\pm 0.10$	.XXX	$\pm 0.5^{\circ}$								