


MAPX	MODIFICATION	DATE



NOTES:

1. HOUSING: SEE NOTES,
TERMINAL: SEE NOTES.
SHELL: SEE NOTES.

SPECIFICATION:

1. ELECTRICAL CHARACTERISTIC:
CONTACT RESISTANCE: $30M\Omega$ MAX
DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN
INSULATION RESISTANCE: $1000M\Omega$ MIN
2. MECHANICAL CHARACTERISTIC:
INSERTION FORCE: 35N(3.57KGF) MAX
EXTRACTION FORCE: $10 \sim 35N(1.02 \sim 3.57KGF)$ MIN
DURABILITY: 1500 CYCLES EXTRACTION FORCE: $10 \sim 35N$
3000 CYCLES MIN
5000 CYCLES EXTRACTION FORCE: $3 \sim 35N$
3. ENVIRONMENTAL:
OPERATING TEMPERATURE: $-55^{\circ}C + 85^{\circ}C$
4. Contact finish:
01: Selective Gold Flash
02: Selective Gold 3U"
03: Selective Gold 5U"
04: Selective Gold 15U"
05: Selective Gold 30U"

<p>产品图 PRODUCT CHART DWG</p> <p>公差一览表 TOLERANCE UNLESS OTHERWISE</p>				单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.		
X.	± 0.25	X.	$\pm 5^{\circ}$	比例 SCALE	1:1	审核 CHKD		产品名称 PRODUCT NO.	C42513	
.X	± 0.20	.X	$\pm 2^{\circ}$	日期 DATE	2015.01.10	核准 APPD		角法 VIEW	版本 VER	
.XX	± 0.15	.XX	$\pm 1^{\circ}$						A0	
.XXX	± 0.10	.XXX	$\pm 0.5^{\circ}$							