







NOTES:

Housing: Thermoplastics,UL94V-0

Contact: Copper Alloy

Shell: Copper Alloy/Steel

Voltage Current Rating:1.5 AMP. 30V AC

Insulation Resistance:1000MΩ Min.

Contact Resistance: 30 MΩ Max.

Dielectric Withstanding Voltage:500W AC

Temperature Range:-35°C to +85°C

Insulator color: Black/White

Plastic material:PBT/LCP/Others

Shell finish:Nickel plated/Tin-Lead plated

Mechanical:

Mating Force:3.5KG MAX

Unmating Force:0.7 KG MIN.

Contact finish:

01: Selective Gold Flash

02: Selective Gold 3U"

03: Selective Gold 5U"

04: Selective Gold 15U"

05: Selective Gold 30U"

产品图 PRODUCT CHART DWG

公差一览表 TOLERANCE UNLESS OTHERWISE			
X.	±0.25	X'.	±5°
.X	±0.20	.X'	±2°
.XX	±0.15	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°

单位 UNITS	MM
比例 SCALE	1:1
日期 DATE	2013.05.10

制图 DRAWING	审核 CHKD	核准 APPD
---------------	------------	------------

Z-Y-B	雷永键	雷永键
-------	-----	-----

产品料号 PRODUCT PART NO.	产品名称 PRODUCT NO.
--------------------------	---------------------

角法 VIEW	版本 VER
------------	-----------

JTJ-USB-AF-180-03	USB-AF10.0 180度鱼叉(带缺口)
-------------------	------------------------

版本 VER	A0
-----------	----