





|            |                      |             |
|------------|----------------------|-------------|
| 目錄<br>MAPX | 設變內容<br>MODIFICATION | 日期<br>DATE  |
| △          | 側彈變更                 | 2013. 3. 10 |



PCB LAYOUT

NOTES:

- Housing: Thermoplastics
- Contact: Copper Alloy
- Shell: Copper Alloy/Steel
- Voltage Current Rating: 1.5 AMP. 30V AC
- Insulation Resistance: 1000MΩ Min.
- Contact Resistance: 30 MΩ Max.
- Dielectric Withstanding Voltage: 500V AC
- Temperature Range: -35°C to +85°C
- Insulator color: Black/White
- Plastic material: PBT/LCP/Others
- Shell finish: Nickel plated/Tin-Lead plated
- Mechanical:
  - Mating Force: 3.5KG MAX
  - Unmating Force: 0.7 KG MIN.
- Contact finish:
  - 01: Selective Gold Flash
  - 02: Selective Gold 3U"
  - 03: Selective Gold 5U"
  - 04: Selective Gold 15U"
  - 05: Selective Gold 30U"

备注：侧弹分为外弹与内弹

|                                     |       |       |       |             |              |               |       |                          |           |
|-------------------------------------|-------|-------|-------|-------------|--------------|---------------|-------|--------------------------|-----------|
| 产品图<br>PRODUCT CHART DWG            |       |       |       |             |              |               |       |                          |           |
| 公差一览表<br>TOLERANCE UNLESS OTHERWISE |       |       |       | 单位<br>UNITS | MM           | 制图<br>DRAWING | Z-Y-B | 产品料号<br>PRODUCT PART NO. |           |
| X.                                  | ±0.25 | X'    | ±5°   | 比例<br>SCALE | 1:1          | 审核<br>CHKD    |       | 产品名称<br>PRODUCT NO.      | C42599    |
| .XX                                 | ±0.15 | .XX'  | ±1°   | 日期<br>DATE  | 2014. 10. 20 | 核准<br>APPD    |       | 角法<br>VIEW               | 版本<br>VER |
| .XXX                                | ±0.10 | .XXX' | ±0.5° |             |              |               |       | 角法<br>VIEW               | A0        |