


USB A/F侧立短体4PIN (B款脚) 无边14.0

| | | |
|-----|--------------|------|
| REV | MODIFICATION | DATE |
| | | |



NOTE:

1. Material:

Housing: Thermoplastics, UL94V-0 (ROHS, HF)
 Contact: Phosphor Bronze C5191-EH/C2680-EH, T=0.25mm
 Shell: COPPER ALLOY T=0.30mm

2. FINISH:

Contact: 15u" Gold Plated on Contact Area,
 80u" Min. Tin Plated on Solder Area
 50u" Min. Nickel Underplating Over All.
 Shell: 50u" Min. Nickel Underplating Over All.

3. Specification:

3.1: Rating:

Rated voltage 500V AC/DC. Rated current: 2 A Max.

3.2: Electrical:

Insulation Resistance(EIA-364-21):
 1000MΩ Min. at 500V/DC for 1Minute.

Contact Resistance(EIA-364-23):
 30 mΩ Max. at 20mV Max, 50mA



Dielectric Withstanding Voltage(EIA-364-20):

No discharge, flashover or breakdown at 500V/AC 1Minute

4. Plug extraction force shall be between 1.0kgf and 2.00kgf

5. Contact finish:

- 01: Selective Gold Flash
- 02: Selective Gold 3U"
- 03: Selective Gold 5U"
- 04: Selective Gold 15U"
- 05: Selective Gold 30U"



| | | | | | | | | | | | |
|-------------------------------------|-------|------|-------|-------------|------------|---------------|-------|--------------------------|--------------------------|----|--|
| 产品图 PRODUCT CHART DWG | | | | | | | | | | | |
| 公差一览表 TOLERANCE UNLESS OTHERWISE | | | | 单位 UNITS | MM | 制图 DRAWING | Z-Y-B | 制图料号 PRODUCT PART NO. | | | |
| X | ±0.25 | X | ±5.° | 比例 SCALE | 1:1 | 审核 CHKD | | 产品名称 PRODUCT NAME | USB A/F侧立短体4PIN (B款脚) 无边 | | |
| .X | ±0.20 | .X | ±2.° | 日期 DATE | 2013.10.31 | 核准 APPD | | 角法 VIEW | 版本 REV | AO | |
| .XX | ±0.15 | .XX | ±1.° | | | | | | | | |
| .XXX | ±0.10 | .XXX | ±0.5° | | | | | | | | |