





目錄 MAPX	設變內容 MODIFICATION	日期 DATE
------------	----------------------	------------

B款



B款



mini-USB-5PIN SOLDER TAIL
焊线式

特性: Specifications

电器 Electrical:

接触阻抗: Contact Resistance

30milliohms MAX

耐电压: Dielectric Withstanding Voltage

500V AC AT sea LeVL

绝缘阻抗: Insulation Resistance:

1000MEGA ohms MIN

材料: Matorial:

塑胶: Housing:Hing Temperature Thermoplastics,
UL 94V-0耐高温塑胶

端子: Contact:Copper Alloy 铜合金

铁壳: Shell:SPCC-SD 铁

电镀: Finish:

端子: Contact: Plated Gold in Mating Area;

Tin/Lead On Solder Talls

接触点镀金, 脚镀锡铅

铁壳: Shell:

Tin/Lead Piating 镀镍

Ordering Informating

X-5-XX

contact plating
01-Gold Flash
02-1-3u"Gold/Tin
03-30u"Gole/Tin

X

Plastic Color
A=Black

产品图 PRODUCT CHART DWG											
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	Z-Y-B	产品料号 PRODUCT PART NO.			
X	±0.15	X'	±5'	比例 SCALE	1:1	审核 CHKD	雷永键	产品名称 PRODUCT NO.	MINI 5P 三件式(大线夹)		
.X	±0.10	.X'	±2'	日期 DATE	2009/07/20	核准 APPD	雷永键	角法 VIEW		版本 VER	40
.XX	±0.05	.XX'	±1'								
.XXX	±0.03	.XXX'	±0.5'								