




RBCOMMENDBD P.C.B PATTBRN LAYD UT

备注：侧弹分为外弹与内弹

NOTES:

Housing: Thermoplastics,UL94V-0

Contact: Copper Alloy

Shell: Copper Alloy/Steel

Voltage Current Rating:1.5 AMP. 30V AC

Insulation Resistance:1000MΩ Min.

Contact Resistance:30 MΩ Max.

Dielectric Withstanding Voltage:500W AC

Temperature Range:-35℃ to +85℃

Insulator color: Black/White

Plastic material:PBT/LCP/Others

Shell finish:Nickel plated/Tin-Lead plated

Mechanical:

Mating Force:3.5KG MAX

Unmating Force:0.7 KG MIN.

Contact finish:

01:Selective Gold Flash

02:Selective Gold 3U"

03:Selective Gold 5U"

04:Selective Gold 15U"

05:Selective Gold 30U"

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.25	X'.	±5'
.X	±0.20	.X*	±2'
.XX	±0.15	.XX*	±1'
.XXX	±0.10	.XXX*	±0.5'

单位
UNITS

MM

制图
DRAWING

Z-Y-B

产品料号
PRODUCT PART NO.

JTJ-USB-AF-08

比例
SCALE

1:1

审核
CHKD

雷永键

产品名称
PRODUCT NO.

USB-AF内扣弯脚

日期
DATE

2009/10/20

核准
APPD

雷永键

角法
VIEW

版本
VER

A0