


■ 技术参数 SPECIFICATIONS

- 线数 (Poles) : 2~24
- 适用线规 (Applicable wires) : AWG28#~22#
- 适应基板厚度 (Applicable PC board thickness) : 1.5~1.6mm
- 温度范围 (Temperature range) : -25℃~85℃
- 额定电压 (Voltage rating) : 250V.Ac/Dc
- 额定电流 (Current rating) : 5A max
- 接触电阻 (Contact resistance) :  $\leq 0.015 \Omega$
- 绝缘电阻 (Insulation resistance) :  $\geq 1000M\Omega$
- 耐压 (Withstand voltage) : 1000V.Ac/1min
- 材料 (Material) :
  - 插头 (Plug Housing) : 尼龙 (PA66) UL94V-2(0)
  - 针座 (Wafer) : 尼龙 (PA66) UL94V-2(0)
  - 端子 (Terminal) : 磷青铜 (Phos.bronze Tin/plated)

HX30002-WA (43045)



针座 WAFER (43045)

线数 Poles	型号 Type		尺寸 Dimensions(mm)		
	直式 (180°)	弯式 (90°)	A	B	C
2	HX30002-2A	HX30002-2WA	0	6.6	0
4	HX30002-4A	HX30002-4WA	3.0	9.6	0
6	HX30002-6A	HX30002-6WA	6.0	12.6	0
8	HX30002-8A	HX30002-8WA	9.0	15.6	4.7
10	HX30002-10A	HX30002-10WA	12.0	18.6	7.7
12	HX30002-12A	HX30002-12WA	15.0	21.6	10.7
14	HX30002-14A	HX30002-14WA	18.0	24.6	13.7
16	HX30002-16A	HX30002-16WA	21.0	27.6	16.7
18	HX30002-18A	HX30002-18WA	24.0	30.6	19.7
20	HX30002-20A	HX30002-20WA	27.0	33.6	22.7
22	HX30002-22A	HX30002-22WA	30.0	36.6	25.7
24	HX30002-24A	HX30002-24WA	33.0	39.6	28.7

# 产品图片

