





A±0.5



P. C. B Layout

一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻: ≤20mΩ
- 1-3. 绝缘电阻: ≥1000MΩ
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度: -55℃~105℃
- 2-2. 焊接温度: +220℃, 10s max

三. 材质:

- 3-1. 塑胶: PBT (Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

Pin	A	B
1	2.00	0.00
2	4.00	2.00
3	6.00	4.00
4	8.00	6.00
5	10.00	8.00
6	12.00	10.00
7	14.00	12.00
8	16.00	14.00
9	18.00	16.00
10	20.00	18.00
11	22.00	20.00
12	24.00	22.00
13	26.00	24.00
14	28.00	26.00
15	30.00	28.00
16	32.00	30.00
17	34.00	32.00
18	36.00	34.00
19	38.00	36.00
20	40.00	38.00
21	42.00	40.00
22	44.00	42.00
23	46.00	44.00
24	48.00	46.00
25	50.00	48.00
26	52.00	50.00
27	54.00	52.00
28	56.00	54.00
29	58.00	56.00
30	60.00	58.00
31	62.00	60.00
32	64.00	62.00
33	66.00	64.00
34	68.00	66.00
35	70.00	68.00
36	72.00	70.00
37	74.00	72.00
38	76.00	74.00
39	78.00	76.00
40	80.00	78.00

未标注公差

XX.	±0.40	XX.°	±2°
X.	±0.30	.XX°	±1°
.X	±0.20		
.XX	±0.15		

绘制: 韩金锋

单位: MM

签发:

比例: 1:1

审核:

视图:



图名: PY2.0-1xNA-4.3MM

图号: XXXXXXXXXXXXXXXXXXXX

Y

B

C

D

E

3

2

1

3

2

1