


REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 03/26/06'		




SPECIFICATION

1. Insulation Resistance:1000MΩ Min.
2. Withstand Voltage:500V AC/Minute.
3. Durability:600 Mating Cycles Min.
4. Product Number Code:

DS1127 - X X X X X


- Housing Materials
P:PBT
N:NYLON
- Housing Color
B:Black
- Contact Plating
0:Gold Flash
3:Selective 3u" Gold
(6;15;30)Micro Inch
- No.Of Contacts
8:10p8c 6:10p6c 10:10p10c
- Connector Type
S:Socket
- Series No.
DS1127



Tel: 86-574-63508787
Fax: 86-574-63510817

(3)	SHIELDING	1	COPPER ALLOY	0.20mm THICKNESS
(2)	PIN		PHOSPHOR BRONZE	GOLD-PLATING
(1)	HOUSING	1	PBT OR NYLON	UL94 V-0 OR 94 V-2
No.	PART NAME	Q'TY	MATERAIL	REMARK

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	±0.60	X.	±5'	mm	PCB JACK 10P
.X	±0.38	.X	±3'	A4	SHEET SIZE
.XX	±0.25	.XX	±2'		SERIES DS1127 ERIES
DRAWING TYPE		CUSTOMER		SCALE	
				1:1 SHEET 1 OF 1	
DRAWING NO.		C-DS1127-XXXX			


晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD

CONNFLY

Add: West Lake Town Cixi Ningbo China
 Tel: 86-574-63508787
 Fax: 86-574-63510817
 E-mail: connfly@connfly.com.cn
 Http://www.connfly.com.cn
 PC: 315321