Panasonic

8 mm Square Long Travel SMD Light Touch Switches

Type: EVQQ1


Features

- External dimensions : 8.5 mm×8.5 mm, Height 6.5 mm (Including the push plate)
- High operating force which prevents incorrect operation
- Reliable contact (dust-proof design)

Recommended Applications

- Switches for car, air conditioners
- Automotive audio equipment
- Steering switches

Explanation of Part Numbers




Specifications

Туре		Snap action/Push-on 1-pole 1-throw SPST				
	Rating	10 µA 2 Vdc to 50 mA 12 Vdc (Resistive load)				
Electrical	Contact Resistance	100 mΩ max.				
	Insulation Resistance	100 M Ω min. (at 100 Vdc)				
	Dielectric Withstanding Voltage	250 Vac for 1 minute				
	Bouncing	10 ms max. (ON, OFF)				
Mechanical	Operating Force	4 N, 5 N				
	Travel	1.0 mm				
Endurance	Operating Life	100000 cycles min.				
Operating Temperature		-40 °C to +85 °C				
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)				
Minimum Quantity/Packing Unit		1000 pcs. Embossed Taping (Reel Pack)				
Quantity/Carton		10000 pcs.				

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


Panasonic

Dimensions in mm (not to scale)



Recommended Reflow Soldering Conditions






Unit: mm

Part No.	Height	А	В	W	F	E	P1	P2	Po	D₀ Dia.	t1	t2
EVQQ1	6.5	8.9±0.2	10.1±0.2	16.0±0.3	7.5±0.1	1.75±0.10	12.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1}	0.40±0.05	6.8±0.2

• Standard Reel Dimensions in mm (not to scale)



Item	А	В	С	D	E		
Rate (mm)	ø380.0±2.0	\$0.0±1.0	<i>ф</i> 13.0±0.5	<i>ф</i> 21.0±1.0	2.0±0.5		
Item	W	Т	t	r			
Rate (mm)	17.5±0.5	21.5±1.0	1.0 to 3.0	1.0±0.5			

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.