

## 贴片NTC热敏电阻(保护器件)

## NTCG063JF103FTB














| 尺寸         |                 |
|------------|-----------------|
| 长度(L)      | 0.60mm ± 0.03mm |
| 宽度(W)      | 0.30mm ± 0.03mm |
| 厚度(T)      | 0.30mm ± 0.03mm |
| 端子宽度(B)    | 0.10mm Min.     |
| 推荐焊盘布局(PA) | 0.30mm ± 0.05mm |
| 推荐焊盘布局(PB) | 0.25mm ± 0.05mm |
| 推荐焊盘布局(PC) | 0.30mm ± 0.05mm |

| 电气特性                  |                  |
|-----------------------|------------------|
| 电阻 [at 25 ° C]        | 10k              |
| 电阻容差                  | ± 1%             |
| B常数(Typ.) [25/50 ° C] | 3380K            |
| B常数(Typ.) [25/85 ° C] | 3435K            |
| B常数(Typ.) [25/100°C]  | 3453K            |
| B常数容差                 | ±1%              |
| 最大电力 [at 25 ° C]      | 100mW            |
| 允许工作电流 [at 25 ° C]    | 310 µ A          |
| 热辐射常数 [at 25°C]       | 1mW/ ° C   1mW/K |

| 其他       |               |
|----------|---------------|
| 最大工作温度   | 125 ° C       |
| 焊接方法     | 回流            |
| UL文件No.  | E250289       |
| AEC-Q200 | No            |
| 包装形式     | 纸编带 (180mm卷筒) |
| 包装个数     | 15000pcs      |
| 重量       | 0.0003g       |

<sup>!</sup> Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.

<sup>!</sup> All specifications are subject to change without notice.

## NTCG063JF103FTB










## **Associated Images**



<sup>!</sup> Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.

<sup>!</sup> All specifications are subject to change without notice.