




P.C.B LAYOUT(Copper-side view)



Model No.	1	2	3
PIN	φ2.0	φ2.35	φ2.5



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3~20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

DRAWN	J.X.Zhang	DATE	2013/11/11	TITLE	PHONE JACKES
CHECKED					
APPROVALS				PART NO.	DC-022
TOLERANCES ARE			30~0.15	±0.30	ANGLE
	10~0.30	±0.20	5~0.10	±0.15	±2°
	~5	±0.10			
				SCALE:	1:1
				DRAWING NO.	
					PROJ.
					SHEET 1 OF 1



ELECTRONICS CO.,LTD