



Model No.	1	2
PIN	∅2.0	∅2.5

Rating: 0.5A 30V DC
 Contact Resistance: 100 mΩ Max.
 Operating temperature: -20°C ~ 70°C
 Operating force: 3-20N
 Operating Life: 5,000 cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

② Terminal	3	Phosphor bronze	Au Plating			
① Housing	1	Nylon	Black			
ITEM	PART NAME	TER. NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE				
DRAWN	J.X.Zhang	2013/11/11				
CHECKED						
APPROVALS			TITLE: PHONE JACKES			
TOLERANCES ARE			PART NO. DC-070			
30±0.1	±0.30	ANGLE	SCALE: 1:1			
10~30	±0.20	UNIT: mm	DRAWING NO.			
5~10	±0.15	±2'	PROJ. SHEET 1 OF 1			
~5	±0.10					



ELECTRONICS CO.,LTD