



Specification
Insulator Material: Polyeser; UL94V-0
Standard: P.B.T
Contact Material: Brass
Contact plated: 0.8u"Gold Over 50u" Nickel

Poles: 2~40P
Current Rating : 3Amp
Contact Resistance: 20 Milliohms Max
Insulation Resistance : 5000MΩ Min.
Dielectric withstanding Voltage: AC 500V
Operation Temperature : -40 °C -- +105°C

APPROVED:		DATE:	
CHECKED:		DATE:	
DRAWN:		DATE:	
LYF		2010-08-12	
TOLERANCE TABLE			
.0	±0.20		
.00	±0.10		
.000	±0.05		
TITLE:		CLIENT P/N	
深圳市旭科盟实业有限公司 CHANKMENG INDUSTRY CO., LTD		/	
210S-1*XP (6.0/2.54/3.0) 蓝胶		UNIT	SCALE
		mm	free
FILE NO.		REV.	A