


Specification
 Insulator Material: Polyeser, UL94V-0
 Standard: PBT
 Contact Material: Brass
 Contact plated: 0.8U" Gold Over Nickel

Poles: 2~40P (Double)
 Current Rating : 3Amp
 Contact Resistance: 20 Milliohms Max
 Insulation Resistance : 1000MΩ Min.
 Dielectric withstanding Voltage: AC 500V
 Operation Temperature : -40 °C -- +105 °C



RECOMMENDED P.C.B LAYOUT

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	TITLE:			
CHECKED:	DATE:	210S-2*XP L=11.6MM			
DRAWN:	DATE:	CLIENT P/N	/	SCALE	free
LXF	2010-08-12	UNIT	mm	REV.	A

深圳市灿科盟实业有限公司
 CHANKEMENG INDUSTRY CO., LTD