

LOW PROFILE HOLDER TYPE CRYSTAL UNITS



Series 49SMD Crystal • E49B



This part is a miniature AT cut strip crystal units with a low profile package. It is with resistance weld.

FEATURES

- Low Cost
- Industry Standard
- Wide Frequency Range
- Excellent Aging

Electrical Specifications


	Туре	E49B		
Frequency Range	F0	3.2~66.000MHz		
Load Capacitance	CL	10pF to Series		
Frenqency Tolerance	△F/ F0	±10ppm,±30ppm,±50ppm(At 25°C)		
Equivalent Series Resistance	ESR	See Table 1		
Temperature Stability	TC	±10ppm,±30ppm,±50ppm(Refer to 25°C)		
Operating Temperature Range	TOPR	-20~+70°C, -30~+85°C Option		
Storage Temperature Range	Tstg	-55~+125°C		
Shunt Capacitance	C0	7pF max.		
Insulator Resistance	IR	500MΩ min. (At 100VDC)		
Drive Level	DL	100μW(500μW max.)		
Aging	Fa	±5ppm max. (At 25°C, First year)		
Packing Unit		200pcs/bag		


Table 1:Equivalent Series Resistance(ESR) and Mode of Vibration(Mode)

Frequency Range(Mhz)	Max ESR(Ω)	Mode	Frequency Range(Mhz)	Max ESR(Ω)	Mode
3.200 to 4.499	150	Fundamental/AT	9.000 to 9.999	60	Fundamental/AT
4.500 to 5.999	120	Fundamental/AT	10.000 to 12.999	50	Fundamental/AT
6.000 to 6.999	100	Fundamental/AT	13.000 to 40.000	40	Fundamental/AT
7.000 to 7.999	90	Fundamental/AT	40.000 to 66.000	80	3 rd Overtone
8.000 to 8.999	80	Fundamental/AT			

^{**}Please contact us for inquiries regarding other Specifications

Mechanical Dimensions(mm)





TAIWAN:

HOSONIC ELECTRONIC CO., LTD. 23-1 LANE 84. CHUN YING ST. SHULIN CHEN. TAIPEI 23804. TAIWAN WEB SITE:http://www.hosonic.com

1: 886-2-86875200 **1**: 886-2-26816456 CHINA: HANGZHOU HOSONIC ELECTRONIC CO., LTD. NO.242 LIANGBO ROAD. LIANGZHU TOWN. YUHANG DISTRICT, HANGZHOU, ZHEJIANG, CHINA

WEB SITE:http://www.hosonic.com

***:** 86-571-88778189 **1**: 86-571-88778857

: hosonic.sales@hosonic.com