



P.C.B LAYOUT

Specification
Insulator Material: Polyeset; UL94V-0
Standard: P.B.T
Contact Material: Brass
Contact plated: Gold Over Nickel

Poles: 2-40P (Double)
Current Rating : 3Amp
Contact Resistance: 20 Milliohms Max
Insulation Resistance : 1000MΩ Min.
Dielectric withstanding Voltage: AC 500V
Operation Temperature : -40 °C -- +105 °C

| | |
|--------|--------|
| 未注公差表 | |
| K, X | ±0.2 |
| K, XX | ±0.10 |
| K, XXX | ±0.050 |

| | | |
|-------|-----------------|--|
| 核准: | 日期: | 深圳市旭科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD |
| 业务: | 日期: | |
| 制图: | 日期: | 品名规格: |
| L Y F | 2008-04-11 | 210R-2*XP (6.0/2.54/1.5/3.0) |
| 客户料号 | 单位 | mm |
| / | 比例 | / |
| 图纸编号: | Ckmtw-210-00003 | 版本 |
| | | A |