



Specification

Insulator Material: Polyacet, UL94V-0

Standard: P.B.T

Contact Material: Brass

Contact plated: 0.8u" Gold Over 50u" Nickel

Poles: 2~40P

Current Rating : 3Amp

Contact Resistance: 20 Milliohms Max

Insulation Resistance : 1000MΩ Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40 °C -- +105 °C

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	C 深圳市灿科盟实业有限公司 kmit™ CHANKEMENG INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE: 210S-1*XP (6.0/2.54/3.0)
LXF	2010-08-12	
CLIENT P/N /		SCALE free
UNIT	mm	
FILE NO.	Chan™-210-00001	REV. A