



Specification
Insulator Material: Polyseter, UL94V-0
Standard: PA6T
Contact Material: Brass
Contact plated: Gold Over Nickel

Poles: 2~40P
Current Rating : 3Amp
Contact Resistance: 20 Milliohms Max
Insulation Resistance : 1000MΩ Min.
Dielectric withstanding Voltage: AC 500V
Operation Temperature : -40℃ -- +105℃

P. C. B. LAYOUT

未注公差表	
X.X	±0.2
X.XX	±0.15
X.XXX	±0.05

核准:	日期:	深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD
业务:	日期:	
制图:	日期:	品名规格:
LYF	2008-04-02	210SMT-2*XP W=7.4MM 塑高2.0
客户料号		单位
/		mm
图纸编号:		比例
Chantw-210-00018		/
版本		版本
A		A