



P.C.B. LAYOUT

**SPECIFICATIONS:**

Current Rating: 2amp  
 Insulator Resistance: 1000Megohms min  
 Dielectric withstanding: AC 500V  
 Operating Temperature: -40° ~ +105°  
 Max Processing Temp: 230° for 30~60 seconds  
 Contact Material: Phosphor Bronze  
 Insulator Material: PA6T UL94V-0  
 Plating: Gold Flash

APPROVED:	DATE:	TITLE: Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	CLIENT P/N /			
DRAWN: LYF	DATE: 2008-04-29	UNIT mm	SCALE Free	REV. A	
TOLERANCE TABLE .0 ±0.30 .00 ±0.20 .000 ±0.05		FILE NO.	Ckmtw-220-20012		