



MATERIAL

Insulator: Polyester ,UL94V-0
 Standard:P.B.T
 CONTACT:Brass
 Contact Plating:Full Gold, Full Tin,
 Selective plating
 Color:Black

SPECIFICATION

Current Rate:3Amp
 Operation Temperature:-40°to +105°
 Contact Resistance:20MmΩ
 MAX.at DC 1A
 Insulation Resistance:1000MΩ
 MIN.atDC500V
 Dielectric Strength:AC500V PER minute

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE: 220R-2*XP H=8.5mm
LXF	2009-05-19	CLIENT P/N /
		UNIT mm
		SCALE free
		FILE NO. Chantw-220-00013
		REV. A