

PRODUCT NO.	DSHPXXTSGER
RoHS compliant	

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electricalife Life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations

2. PLATING:  
GOLD FLASH 1u”(min.) SOLDERTAIL,  
3u” GOLD PLATING ON THE CONTACT AREA,  
WITH 50u” NICKEL UNDERPLATINGOVERALL.
3. PART NUMBER DESCRIPTION :

DSHP XX I S G E R

[包装方式: T=管装 R=Reel]






[电键层: B=镀镍3u”焊脚部1.2u” G=镀镍3u”焊脚部3u” F=镀镍10u”焊脚部10u”]

[G=镀全金 S=内镀金(接触部)外镀锡(焊脚部)]


[脚型: S脚 / J脚 / 圆脚 / A脚 / 2脚]

[T=低推贴胶 S=低推不贴胶 L=长推]


[产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



POS.	DIMENSIONS	
	A	B
2P	1.27	4.14
3P	2.54	5.41
4P	3.81	6.68
5P	5.08	7.95
6P	6.35	9.22
8P	8.89	11.76
10P	11.43	14.30



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	3u” Gold
④	Terminal	Brass	1u” Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u” Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		ANGLES		PROJECTION	
0 ± 0.25	0 ± 2'	0 ± 0.10	0.00± 0.5'	INSPECTION COPY	
DRAWING				BY DSHP SERIES PITCH 1.27mm	
CHECK				PRODUCT FAMILY DSHP SERIES	
APPRO.				PRAT NO. DSHPXXTSGER	
FILE NO. DSHPXXTSGER-A				SIZE UNIT SCALE SHEET REV.	
A4 mm				2 : 1 1OF 1 A	

**东莞市广智实业有限公司**  
Dongguan Kingtek Industrial Co., Ltd.