








PRODUCT NO. DS1C03TSGER	NO. Rohs compliant
-----------------------------------	------------------------------



RECOMMENDED P. C. B. LAYOUT (TOP VIEW)



- NOTES :**
- 1>.Specification:
 - 1>.Operating force:1000gf Max
 - 2>.Operating Temperature: -40° to+85°
 - 3>.Storage Temperature: -40° to+85°
 - 4>.Mechanical Life:3000cycles minimum
 - 5>.Electrical Life:2000cycles 25mA 24VDC
 2. PLATING:
 - GOLD FLASH 1u"(min.) SOLDER TAIL,
 - 3u" GOLD PLATING ON THE CONTACT AREA,
 - WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION

DS1C XX I S G E R
 [包装方式: I=管装 R=盒装]
 [电镀层: B=镀锡3u" G=镀镍3u" / 镀镍3u" / 镀镍3u"-2u"]
 [G=鍍金 S=內金外鍍]
 [脚型: S脚 / J脚 / 0脚 / A脚 / Z脚]
 [T=低接触度 S=低接触度 L=长推]
 [产品号: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]

Number	Part Name	Material	Finished
①	Actuator	UL94 VO	White
②	Cover	UL94 VO	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 VO	Black
⑥	Terminal Contact	Brass	3u"Gold
⑦	Myar	UL94 VO	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		IN/INSPECTION COPY	
LINER	ANGLES	PROJECTION	COPY
0 ± 0.25	0. ± 2'	0	
.00 ± 0.15	.0 ± 1'	0.00 ± 0.10	
.000 ± 0.10	.00 ± 0.5'	DESIGN	2012/04/12
DRAWING		PRAT NO.	DS1C03TSGER
CHECK		FILE NO.	DS1C03TSGER-A
APPRO.		SIZE	UNIT SCALE SHEET REV.
		A4	m/m 2 : 1 1OF 1 A

RE 东莞市广辉实业有限公司
 Dongguan Kingtek Industrial Co., Ltd.

TITLE
 BY DSIC SERIES PITCH 2.54mm
 PRODUCT FAMILY DSIC SERIES

PRAT NO. DS1C03TSGER
 FILE NO. DS1C03TSGER-A
 SIZE UNIT SCALE SHEET REV.
 A4 m/m 2 : 1 1OF 1 A