







PRODUCT NO.	1
RoHS compliant	2

REV.	BCN NO.	DR	DATE




- NOTES :
- 1> Specification:
    - 1> Operating force: 1000gf Max
    - 2> Operating Temperature: -40° to +85°
    - 3> Storage Temperature: -40° to +85°
    - 4> Mechanical Life: 3000cycles minimum
    - 5> Electrical Life: 2000cycles 25mA 24VDC
  2. PLATING:
    - GOLD FLASH 1u"(min.) SOLDER TAIL,
    - 3u" GOLD PLATING ON THE CONTACT AREA,
    - WITH 50u" NICKEL UNDERPLATING OVERALL.
  3. PART NUMBER DESCRIPTION

DISC XX I S G E R

[包装方式: T=管装 R=Roll]  
 [电镀层: B=镀锡3u" G=镀金3u" P=镀银1-2u"]  
 [G=镀金 S=内金外镀]  
 [脚型: S脚 / J脚 / 直脚 / A脚 / Z脚]  
 [T=低档封装 S=低档封装 L=长插]  
 [产品代码: 02-2P 04-4P 06-6P 08-8P 10-10P 12-12P]

RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished
①	Actuator	UL94 VO	White
②	Cover	UL94 VO	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 VO	Black
⑥	Terminal Contact	Brass	3u"Gold
⑦	Mylar	UL94 VO	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY
LINER	ANGLES	PROJECTION
0 ± 0.25	0 ± 2°	
.00 ± 0.15	.0 ± 1°	
.000 ± 0.10	.00 ± 0.5°	
DESIGN	kathy	2012/04/12
DRAWING		
CHECK		
APPRO.		

**KE** 东莞市广誉实业有限公司  
Dongguan Kingtek Industrial Co., Ltd.

TITLE  
BY DISC SERIES PITCH 2.54mm  
PRODUCT FAMILY DISC SERIES  
PRAT NO. DISC10TSGER  
FILE NO. DISC10TSGER-A  
SIZE UNIT SCALE SHEET REV.  
A4 mm 2 : 1 1 OF 1 A