







PRODUCT NO. DSDT08LHGET
RoHS compliant

REV.	ECN NO.	DR	DATE
A	New	H H	14/12/31



POS.	DIMENSIONS	
	A	B
4P	11.64	7.62
5P	14.18	10.16
8P	21.80	17.78
9P	24.34	20.32
10P	26.88	22.86



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u"Gold

TOLERANCE UNLESS OTHERWISE SPECIFIED			INSPECTION COPY	
LINER	ANGLES	PROJECTION	COPY	
0 ± 0.25	0 ± 2'			
.00 ± 0.15	.0 ± 1'			
.000 ± 0.10	.00 ± 0.5'			
DESIGN	CHI HUAI HE	2015/01/22		
DRAWING				
CHECK				
APPRO.				
东莞市广誉实业有限公司 Dongguan Kingtek Industrial Co., Ltd.			TITLE BY DSDT SERIES PITCH 2.54mm PRODUCT FAMILY DSDT SERIES PRAT NO. DSDT08LHGET	
FILE NO.	DSDT08LHGET-A	SIZE	UNIT	SCALE
A4	mm	1 : 1	10F 1	A

NOTES :

- Specification:
 - Operating force: 1000g/f Max
 - Mechanical Life: 3000cycles minimum
 - Electrical Life: 2000cycles minimum
- Contact Rating:
 - Switching: 25mA, 24VDC
 - Non Switching: 100mA, 50VDC
- Contact Resistance:
 - Initial: 50mOhm Max.
 - After Life Test: 100mOhm Max.

2. PLATING:
 GOLD FLASH 1u"(min.) SOLDER TAIL,
 3u" GOLD PLATING ON THE CONTACT AREA,
 WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION

DSDT XX L H G E T

- [包装方式: L=管装 R=Reel]
- [电镀层: E=接触部3u" G=接触部3u" /焊接触部1-2u"]
- [G=镀金 S=内金外镀]
- [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品P数: 08-8P]