


PCB Layout(Pattern side)

NOTE:
 Operating Force: 500 ± 50 gf
 Travel: 15 Pulses $0.3\text{mm} \pm 0.1\text{mm}$



Circuit Diagram

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑩	Dust cover	—	1	Kapton Film	Yellow	—
⑨	Spring plate	—	1	SUS	Natural	—
⑧	Contact	—	1	F.Ag/SUS	Natural	—
⑦	Knob	—	1	LCP	Black	—
⑥	Tuning Knob 2	—	1	LCP	Black	—
⑤	Terminal	—	8	Brass(0.15t)	Plating silver	—
④	Gasket	—	1	Aluminum	Plating Stannum	—
③	Base	—	1	LCP	Black	—
②	Earth Terminal	—	1	Brass(0.15t)	Plating silver	—
①	Tuning Knob 1	—	1	LCP	Black	—

APPROVALS		DATE	HRO 華榮 ELECTRONICS CO.,LTD						
DRAWN	J.X.Zhang	2013/7/25	TITLE:	MULTIFUNCTIONAL SWITCHES					
CHECKED			PART NO.	K1-1203UA-01					
APPROVALS			TOLERANCES ARE	30~以上: ± 0.30 10~30: ± 0.20 5~10: ± 0.15 ~ 5: ± 0.10	ANGLE	$\pm 2'$	UNIT: mm	SCALE: 1:1	PROJ:
			DRAWING NO.			SHEET 1 OF 1			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			