


PCB Layout(Pattern side)



- Note:
1. Rating : DC 12V 50mA
 2. Contact Resistance : ≤50mΩ
 3. Insulation Resistance: DC500V 1Minute
 4. Operating Temperature Range: -25℃+80℃
 5. Ambient Humidity Used: ≤85%RH
 6. Operating Force : 150±80gf
 7. Operating Life : 50,000Cycles

ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Beryloy	Ag Plated	—
④	Terminal	—	5	Phosphor Bronze	Ag Plated	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	Natural	—
①	Knob	—	1	PA46	RED	—

APPROVALS		DATE	TITLE:	
DRAWN	JKUN.LU	2013/10/8	ELECTRONICS CO.,LTD	
CHECKED			TOGGLE SWITCHES	
APPROVALS			PART NO. K3-1288S	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ:	SHEET
	A		NEW				30~0.1±	±0.30	mm	1:1	PROJ: 1288S	1 OF 1
							10~0.30	±0.20				
							5~1.0	±0.15				
							~5	±0.10				