



P.C.B layout



Circuit Diagram



NOTE:
1. Operating force: 200±50gf

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Knob	—	1	NYLON	Black	—
④	Cover	—	1	SUS	—	—
③	Base	—	1	PA66	Black	—
②	Contact Clip	—	4	PBS C5210R-EH	Ag Clad	—
①	Terminal	—	12	Brass Strip	Ag Plated	—

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2014/09/11				
CHECKED				TITLE:		TOGGLE SWITCHES
APPROVALS				PART NO.		K3-2268D-F1
TOLERANCES ARE		30~以下	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			
		5~10	±0.15	±2'	DRAWING NO.	PROJ:
		~ 5	±0.10			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—