



NOTE:
 Rating: DC 30V 0.1A
 Operating Force: 40±10gf
 Lifetime: 100,000 Cycles

PART NO.	H
K5-1130SA-01	8.5
K5-1130SA-02	11.0
K5-1130SA-03	12.3
K5-1130SA-04	13.7

Circuit Diagram

Detail of P (SCALE: 2:1)

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Phosphor Bronze	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Base	—	1	NYLON	Black	—
②	Cover	—	1	NYLON	Black	—
①	Knob	—	1	NYLON	Black	—

APPROVALS		DATE	TITLE:
DRAWN	JKUN.LU	2015.03.17	DETECTOR SWITCHS
CHECKED			
APPROVALS			

TOLERANCES ARE		ANGLE	UNIT:	SCALE:	DRAWING NO.	SHEET
30~ø12.1	±0.30	±2°	mm	1:1		1 OF 1
10~ø30	±0.20					
5~ø10	±0.15					
~5	±0.10					

HRON
 ELECTRONICS CO.,LTD