



NOTE:  
 Rating: DC 30V 0.1A  
 Operating Force: 20±10gf  
 Lifetime: 50,000 Cycles

ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Be Alloy	Ag Plated	—
④	Terminal	—	2	Phosphor Bronze	Ag Plated	—
③	Cover	—	1	SUS	Natural	—
②	Housing	—	1	LCP	Black	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhang	2013/8/26	ELECTRONICS CO.,LTD	
CHECKED			DETECTOR SWITCHS	
APPROVALS			PART NO.	K5-1617SA-02

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
			30~0.1L	±0.30	ANGLE	PROJ.
			10~30	±0.20	UNIT: mm	SCALE: 1:1
			5~10	±0.15	±2'	DRAWING NO.
			~5	±0.10		SHEET 1 OF 1