


NOTE:

- 1. Rating: AC125V 5A/250V 3A
- 2. Operating force: 100±30gf
- 3. Mechanical Life: 100,000
- 3. Electrical Life: 6000-10,000



Circuit Diagram

⑧	Shrapnel 2	—	1	Copper Alloy	—	—
⑦	Shrapnel 1	—	1	Beryllium Copper	—	—
⑥	Contact	—	1	Copper Alloy	Plating silver	—
⑤	Aluminum rivet	—	1	Aluminum Alloy	—	—
④	Terminal	—	3	Copper Alloy	Plating silver	—
③	Housing	—	1	PBT	Black	—
②	Knob	—	1	PBT	Black	—
①	Cover	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2014/8/19				
CHECKED				TITLE: MICRO SWITCHS		
APPROVALS				PART NO. K9-1910B		
TOLERANCES ARE		30~以下	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~20	±0.25			
		5~10	±0.20	±2'	DRAWING NO.	PROJ:
		~ 5	±0.20			
SHEET 1 OF 1						

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.