


NOTE:

- 1. Rating: AC125V 5A/250V 3A
- 2. Operating force: 30±10gf
- 3. Mechanical Life: 1,000,000
- 3. Electrical Life: 6000-10,000



Circuit Diagram

ITEM	PART NAME	TER. NO.	QTY.	MATERIAL	FINISHING	REMARK
8	Shrapnel 2	—	1	Copper Alloy	—	—
7	Shrapnel 1	—	1	Beryllium Copper	—	—
6	Contact	—	1	Copper Alloy	Plating silver	—
5	Lever	—	1	Stainless Steel	—	—
4	Terminal	—	3	Copper Alloy	Plating silver	—
3	Housing	—	1	PBT	Black	—
2	Knob	—	1	PBT	Black	—
1	Cover	—	1	PBT	Black	—

APPROVALS		DATE		 <b>ELECTRONICS CO.,LTD</b>			
DRAWN	J.X.Zhang	2014/8/19					
CHECKED				TITLE:	MICRO SWITCHS		
APPROVALS				PART NO.	K9-1910C		
TOLERANCES ARE		30~以下	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
		10~20	±0.25		DRAWING NO.		SHEET 1 OF 1
		5~10	±0.20	±2'			
		~ 5	±0.20				

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.