



P.C.B LAYOUT(Copper-side view)



DC MATE PLUG

Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

②	Terminal	5	Phosphor bronze	Au Plating		
①	Housing	1	Nylon	Black		
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE				
DRAWN	J.X.Zhang	2013/11/11	TITLE: PHONE JACKES			
CHECKED			PART NO. DC-098			
APPROVALS			SCALE: 1:1			
TOLERANCES ARE		30~80μm	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			PROJ.
		5~10	±0.15	±2'	DRAWING NO.	SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.			
	A		NEW			



ELECTRONICS CO.,LTD