




P.C.B LAYOUT(copper-sided view)



Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

② Terminal	3	Phosphor bronze	Au Plating			
① Housing	1	Nylon	Black			
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS	DATE	ELECTRONICS CO.,LTD				
DRAWN	J.X.Zhang	2013/11/11	PHONE JACKES			
CHECKED			DC-072			
APPROVALS			PART NO.			
TOLERANCES ARE	30~0.15	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ. SHEET 1 OF 1
	10~0.30	±0.20				
	5~0.10	±0.15	±2'	DRAWING NO.		
	~ 5	±0.10				