



P.C.B LAYOUT TOP VIEW



SCHEMATIC

PIN	Ø 1.65	Ø 2.0	Ø 2.5
APPD			

Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3~20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																											
	A		NEW																																																																														
<table border="1"> <tr> <td>② Terminal</td> <td>—</td> <td>3</td> <td>Phosphor bronze</td> <td>Au Plating</td> <td>—</td> </tr> <tr> <td>① Housing</td> <td>—</td> <td>1</td> <td>Nylon</td> <td>Black</td> <td>—</td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER.NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td>DATE</td> <td colspan="4">TITLE: PHONE JACKES</td> </tr> <tr> <td>DRAWN</td> <td>J.X.Zhang</td> <td>2013/11/11</td> <td colspan="4">ELECTRONICS CO.,LTD</td> </tr> <tr> <td colspan="2">CHECKED</td> <td></td> <td colspan="4">PART NO. DC-028S</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td></td> <td colspan="4">SCALE: 1:1</td> </tr> <tr> <td colspan="2">TOLERANCES ARE</td> <td>30~0.15</td> <td>±0.30</td> <td>ANGLE</td> <td>UNIT: mm</td> <td>PROJ. </td> </tr> <tr> <td colspan="2"></td> <td>10~0.20</td> <td>±0.20</td> <td></td> <td>DRAWING NO.</td> <td>SHEET 1 OF 1</td> </tr> <tr> <td colspan="2"></td> <td>5~0.10</td> <td>±0.15</td> <td>±2'</td> <td></td> <td></td> </tr> <tr> <td colspan="2"></td> <td>~ 5</td> <td>±0.10</td> <td></td> <td></td> <td></td> </tr> </table>							② Terminal	—	3	Phosphor bronze	Au Plating	—	① Housing	—	1	Nylon	Black	—	ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE	TITLE: PHONE JACKES				DRAWN	J.X.Zhang	2013/11/11	ELECTRONICS CO.,LTD				CHECKED			PART NO. DC-028S				APPROVALS			SCALE: 1:1				TOLERANCES ARE		30~0.15	±0.30	ANGLE	UNIT: mm	PROJ.			10~0.20	±0.20		DRAWING NO.	SHEET 1 OF 1			5~0.10	±0.15	±2'					~ 5	±0.10			
② Terminal	—	3	Phosphor bronze	Au Plating	—																																																																												
① Housing	—	1	Nylon	Black	—																																																																												
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK																																																																											
APPROVALS		DATE	TITLE: PHONE JACKES																																																																														
DRAWN	J.X.Zhang	2013/11/11	ELECTRONICS CO.,LTD																																																																														
CHECKED			PART NO. DC-028S																																																																														
APPROVALS			SCALE: 1:1																																																																														
TOLERANCES ARE		30~0.15	±0.30	ANGLE	UNIT: mm	PROJ.																																																																											
		10~0.20	±0.20		DRAWING NO.	SHEET 1 OF 1																																																																											
		5~0.10	±0.15	±2'																																																																													
		~ 5	±0.10																																																																														