




Model No.	DC-099-1	DC-099-2
PIN	φ2.0	φ2.5



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles



②	Terminal	—	2	Phosphor bronze Au Plating
①	Housing	—	1	Nylon Black
ITEM	PART NAME	TERN.O.	QTY.	MATERIAL FINISHING
APPROVALS		DATE		
DRAWN	J.X.Zhong	2013/11/11		

TITLE: PHONE JACKES

CHECKED		TITLE:	PHONE JACKES
APPROVALS		PART NO.	DC-099

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30~12.5 ±0.30	10~30 ±0.20	5~10 ±0.15	~5 ±0.10	ANGLE	±2°	UNIT: mm	SCALE: 1:1	PROJ:	SHEET 1 OF 1
	A		NEW														

